

LDM-4 Standard Module



Features

- Compact size (11mm dia. x 25mm long)
- Slow start, reverse polarity and over voltage protection
- Good collimation
- Large range of options

The LDM-4 Standard Module offers a versatile and cost effective solution suited to a wide range of applications such as bore sighting, alignment, safety systems, robot control, positioning and detection.

The LDM-4 provides a well collimated laser light source, and includes provision for laser line generators and a range of other optical options to suit most requirements.

The electronics circuitry provides slow start, reverse polarity and over voltage protection and is available with a pulsing option if required. Power is connected to the module using red (+ve) and blue (-ve) flying leads. The red (+ve) lead is also connected to the modules case.

Specifications:

Available Wavelengths	635, 650, 670, 780, 808, 830 & 850nm
Available Powers	1 - 200mW
Beam Size at aperture	3mm diameter
Divergence (collimated beam)	< 0.75mrad
Operating voltage	3 - 6V DC
Operating current	30 - 300mA (Depending on laser power)

Specify part numbers as follows: **LDM-4P-650-3-L90**

(i.e. LDM-4 series, pulsed option, wavelength = 650nm, output power = 3mw, 90 deg. line generator)

Options

Collimated beam for pointing	C
100kHz Pulsed option	P
Fixed Focus	F300 (Focussed at distance of 300mm)
Variable Focus	V
Heat Protective Glass	HG
Cross Hair	CH
Line Generator	L30, L45, L60 & L90 (L30 = 30 deg. fan angle)

This product is registered with the FDA in accordance with 21 CFR 1040.10(a)(3)(I) and is compliant with European, and Australia/New Zealand laser safety standards 73/23/EEC - 98/37/EG, 89/336/EEC, EN 50081-1, EN-31252, EN-31252, EN 55022, EN 60825-1 and AS/NZS 2211:1997. The complete laser product manufacturer must supply adequate instructions for installation and servicing of this product. This is not a removable laser system. This product is designed solely as a component in an electronic product and therefore does not comply with the requirements of 21 CFR 1040.10 and 1040.11 for complete laser products. Avoid direct eye exposure to the beam.

Distributed By ...



www.AINNOTECH.com

Email: korea@ainnotech.com

TEL: 02,409,3222 FAX: 02,409,3229

서울시 송파구 가락동 10-9 현성 B/D 2F